



Astronomical Time switch, 1 Channel

Technical Characteristics

Fixing mode	Din-Rail
Function	Keylock by means of blocking key
Frequency	50/60 Hz
Supply voltage	230V +10% / -15%
Maximum connection distance between receiver and transmitter	
Breaking capacity	16A 250V AC1
Supply voltage	230 V +/- 15%
Max. power fluo. duo lamp comp. series	1000 W
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of contacts	1 changeover contact floating
Type of connection	with screw terminals
Summer / Winter time change	automatic
Shortest switching time	1 mn
Astronomic program	1
Type of display	
Supply failure reserve	5 years
With holidays program	No
Cycle	weekly
Protection index IP	IP20
Working accuracy	1,5