



RCBO Electronic 1P 10kA C Curve-20A, 30mA Type A(AC & Pulsating DC Sensitive)1M

Technical Characteristics

Neutral position	right
Type of pole	1 P
Fixing mode	
Curve	C
Frequency	50 Hz
Colour	
Tightening torque	2,1Nm
Connection cross-sect. flexible conductor	
Connection cross-sect. rigid cable	
Type of connection	
European directive WEEE	concerned
Protection index IP	IP20
Residual current type	A