

# ACC125

RCBO Electronic 1M 1P 10kA C-25A 10mA AC Class



- Architecture
  - Neutral position  
right
  - Number of poles  
1 P
  - Type of pole  
1 P
  - Curve  
C
- Main electrical features
  - Frequency  
50 Hz
  - Rated current  
25 A
- Voltage
  - Rated insulation voltage  
250 V
  - Max operating voltage  
253 V
  - Rated impulse withstand voltage  
4000 V
- Electric current
  - Breaking and opening capacity  
6 kA
- Electric current / temperature
  - Rating current 30°C  
25 A

- Dimensions
  - Depth of installed product  
73 mm
  - Height of installed product  
115 mm
  - Width of installed product  
17.8 mm
- Power
  - Total power loss under IN  
6.9 W
- Endurance
  - Electric endurance in number of cycles  
2000
  - Number of mechanical operations  
1000
- Capacity
  - Number of modules  
1
- Installation, mounting
  - Tightening torque  
2,1Nm
- Standards
  - Standard text  
EN 61009-1  
IEC 61009-1
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP20
  - Residual current type  
AC
- Temperature
  - Operating temperature  
-5/60 °C