

ACA190U

RCBO Electronic 1M 1P 10kA C-40A 10mA A Class



- Architecture
 - Neutral position
right
 - Number of poles
1 P
 - Type of pole
1 P
 - Fixing mode
DIN rail type O (symmetrical)
 - Curve
C
- Main electrical features
 - Frequency
50 Hz
 - Rated current
40 A
- Voltage
 - Rated insulation voltage
250 V
 - Max operating voltage
253 V
 - Rated impulse withstand voltage
4000 V
- Electric current
 - Breaking and opening capacity
6 kA
- Electric current / temperature

- Rating current 30°C
40 A
- Dimensions
 - Depth of installed product
70 mm
 - Height of installed product
110 mm
 - Width of installed product
17.8 mm
- Power
 - Total power loss under IN
12.96 W
- Endurance
 - Electric endurance in number of cycles
2000
 - Number of mechanical operations
1000
- Capacity
 - Number of modules
1
- Installation, mounting
 - Tightening torque
2,1Nm
- Standards
 - Standard text
EN 61009-1
IEC 61009-1
 - European directive WEEE
concerned
- Safety
 - Protection index IP
IP20
 - Residual current type
A
- Temperature
 - Operating temperature
-5/60 °C