



Electronic earth leakage add-on block 3P 160A I_{dn} adjustable, time delay

Technical Characteristics

Neutral position	not applicable
Number of poles	3 P
Fixing mode	DIN rail type O (symmetrical)
Rated operational voltage U _e	415 V 220 V
Rated current	160 A
Rated insulation voltage	500 V
Rated impulse withstand voltage	6 kV
Rated residual operating current	100 mA 1 A 30 mA 6 A 3 A 300 mA
European directive WEEE	concerned
Protection index IP	IP4X
Residual current type	A HI