

HBA125H

Electronic earth leakage add-on block 3P 125A I_{dn} adjustable, time delay



- Architecture
 - Neutral position not applicable
 - Number of poles 3 P
 - Fixing mode DIN rail type O (symmetrical)
- Main electrical features
 - Rated current 125 A
- Voltage
 - Rated insulation voltage 500 V
 - Rated impulse withstand voltage 6 kV
- Standards
 - European directive WEEE concerned
- Safety
 - Protection index IP IP4X
 - Residual current type A HI