



### Auxiliary contact 1NC+1NO

#### Technical Characteristics

Rated operational voltage Ue	250 V
Rated current	2 A
Rated insulation voltage	250 V
Depth of installed product	58 mm
Height of installed product	83 mm
Width of installed product	8.75 mm
Total power loss under IN	0.1 W
Number of modules	0.5
Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of connection	with screw
Number of contacts	2
Type of contacts	1NC+1NO
Can be accessorized	No
European directive WEEE	concerned
Operating temperature	-40 °C -5 °C