

P22/LSF/1.0

P22 c/w 3 Core 0.75mm² 1 Metre LSOH Lead



[More Information](#)

Approvals	BS 6972:1988
Type of finished cable	Device connection cable
Conductor cross-section (flexible), with wire end sleeve	0.75 mm ²
Rated current	6 A
Cable length	1000 mm
Dismantle length	50 mm
Strip length	7 mm
Total length	1 m
Material	Mixed
Number of terminations -plugs	3
Protection classes/types	IP20__PROTECTION-SYMBOL.EPS
Conductor Size	0.75 mm ²
Cable permanent temperature-resistant to	90 °C
Inflammability	UL 94 V0
Cable End	Prepared - end of barrel closed
Cable Material	Low Smoke Zero Halogen

Contact Material	Phosphor Bronze
Mechanical Load	5 Kg maximum
Colour	pure white
Type side 1	Plug
Type side 2	Free conductor end
Application, usage	Light control
Rated operational voltage Ue	207 / 230 / 253 V
Unit	PCE
EAN	5015652041887
Sales status	3C