



## Bar/Cable-through Current Transformer BG 113 100/5A 2,5VA Class 1

### Technical Characteristics

Fixing mode	Din-Rail or on a fixing plate
Frequency	50/60 Hz
Rated insulation voltage	3 kV
Depth of installed product	30 mm
Height of installed product	70 mm
Width of installed product	49.5 mm
Height of opening	20 mm
Total power loss under IN	0.7 W
Connection cross-sect. flexible conductor	1,5 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 6mm <sup>2</sup>
Type of connection	screw
European directive WEEE	concerned
Protection index IP	IP10
Operating temperature	40 °C