



Multi-order thermostat

Technical Characteristics

Fixing mode	Din-Rail
Function	with frost protection function
Frequency	50/60 Hz
Supply voltage	230V +10 / -15%
Maximum connection distance between receiver and transmitter	50m
Breaking capacity	2A 250V AC1
Supply voltage	
Mounting type	
Connection cross-sect. flexible conductor	1 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 10mm ²
Type of contacts	1 changeover
Type of connection	with screw terminals
Comfort temperature setpoint	5 / 30 °C
Temperature range	5 / 30°C
Type of display	
Type of programmable thermostat	Analog
Type of probe	
Protection index IP	IP40
Frost protection temperature setting	5 / 30 °C