



Night & Day Contactor 40A, 3NO, 230V~50Hz

Technical Characteristics

Frequency	50 Hz
Type of lamp	
Max. power fluo. duo lamp comp. series	
Tightening torque	Coil: 2,5Nm ; Power: 3,5Nm
Connection cross-sect. flexible conductor	4 / 16mm ²
Connection cross-sect. rigid cable	4 / 25mm ²
Type of connection	with screw
Type of contacts	3NO
Can be accessorized	Yes
European directive WEEE	concerned
Protection index IP	IP2X
Protection class	isol.class II