

# ETC225S

Humfree Night & Day Contactor 25A, 2NO, 230V~50/60Hz



- Main electrical features
  - Frequency  
50/60 Hz
  - Rated current  
25 A
- Voltage
  - Rated insulation voltage  
250 V
  - Rated impulse withstand voltage  
4 kV
- Dimensions
  - Depth of installed product  
64 mm
  - Height of installed product  
83 mm
  - Width of installed product  
17.85 mm
- Power
  - Total power loss under IN  
5.2 W
  - Power dissipation per coil  
2.2 W
- Endurance
  - Electric endurance in number of cycles  
30000
  - Number of mechanical operations  
100000

- Capacity
  - Number of modules  
1
- Fluorescent bulbs control
  - Max. power with fluorescent parallel lamps  
810 VA
- Incandescent bulbs control
  - Max. power with incandescent lamps  
1900 W
- Installation, mounting
  - Tightening torque  
1,2Nm
- Connection
  - Connection cross-sect. flexible conductor  
1 / 6mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1 / 10mm<sup>2</sup>
  - Type of connection  
with screw
  - Type of contacts  
2NO
- Equipment
  - Can be accessorized  
Yes
- Standards
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP2X
- Use conditions
  - Storage temperature  
-40/80 °C
- Temperature
  - Operating temperature  
-10/50 °C