

Product data sheet

CR64AX/4.0

:hager



CR64AX c/w 4 Core 0.75mm² 4m PVC Lead

Technical Characteristics

	253 V
	207 V
Rated operational voltage U _e	230 V
Rated current	6 A
Colour	pure white
Cable End	Prepared - end of barrel closed
Conductor Size	0.75 mm ²
Cable Material	PVC
Cable Standard	BS 6141
Number of terminations -sockets	5
Number of terminations -plugs	4
Contact Material	Phosphor Bronze
Mechanical Load	5 Kg maximum
Inflammability	UL 94 V0
Application, usage	Light control