

# Product data sheet

CR64AX/1.0

**:hager**



## CR64AX c/w 4 Core 0.75mm<sup>2</sup> 1m PVC Lead

### Technical Characteristics

	207 V
	230 V
Rated operational voltage U <sub>e</sub>	253 V
Rated current	6 A
Colour	pure white
Cable End	Prepared - end of barrel closed
Conductor Size	0.75 mm <sup>2</sup>
Cable Material	PVC
Cable Standard	BS 6141
Number of terminations -sockets	5
Number of terminations -plugs	4
Contact Material	Phosphor Bronze
Mechanical Load	5 Kg maximum
Inflammability	UL 94 V0
Application, usage	Light control