



### Multi-range thermostat

#### Technical Characteristics

Fixing mode	
Function	with frost protection function ; 3 function options in case of sensor failure by wire jumper setting
Frequency	50/60 Hz
Supply voltage	230V +10 / -15%
Maximum connection distance between receiver and transmitter	50m
Breaking capacity	2A 250V AC1
Supply voltage	230 V +10% / -15%
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
Type of connection	with screw
Type of contacts	1 changeover
Type of connection	with screw terminals
Comfort temperature setpoint	5 / 30 °C
Temperature range	-30 / +90°C
Type of display	
Type of programmable thermostat	Analog
Type of probe	separated sensor
Protection index IP	IP40
Frost protection temperature setting	-30 / 90 °C