

EE811

Presence detector 360°, 2 channels, flush mounted, white

Architecture

Fixing mode section make

Functions

Function Linking with 1-channel presence detectors in order to expand the detection area

Main electrical features

Rated operational voltage Ue 230 V

Frequency 50 Hz

Dimensions

Length 100 mm

Frequency

Frequency 50 Hz

Power

Incandescent bulb power 0 / 1500 W

Capacity

Breaking capacity	16A 250V AC1
Reach distance	
Max. transmission range	12m
Power supply	
Supply voltage	230 V
Detection	
Side detecting distance	13 m
Detection angle	360 °
Materials	
Colour	pure white
Lighting control	
Brightness measurement range	5 / 1200 Lux
Installation, mounting	
Maximum Mounting Height	4 m
Connection	
Connection type	1 to 4 mm ²
Type of contacts	1NO
Settings	
Time delayed range	1 ; 30min
Response value sensitivity adjustable	Yes
Scope of delivery	
Component	with flush-mounted switch insert
Safety	
Protection index IP	IP41
Protection class	isol.class II
Use conditions	
Operating temperature	0/45 °C
Storage temperature	-10/60 °C
Temperature	
Operating temperature	0/45 °C
Identification	
Application, usage	Motion detector