

# EV004

## Universal dimmer comfort 600W



- Architecture
  - Fixing mode  
Din-Rail
- Main electrical features
  - Frequency  
50 Hz
  - Rated current  
2.6 A
- Voltage
  - Supply voltage  
230V +/- 10%
- Dimensions
  - Depth of installed product  
58 mm
  - Height of installed product  
85 mm
  - Length  
58 mm
  - Width of installed product  
7.1 cm
- Power
  - Total power loss under IN  
6 W
  - Power dissipation per coil  
1.3 W
- Capacity
  - Number of modules

4

- Connection
  - Connection cross-sect. flexible conductor  
1 / 16mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1,5 / 10mm<sup>2</sup>
  - Type of load  
universal
  - Type of connection  
with screw
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-20/60 °C
- Temperature
  - Operating temperature  
-10/45 °C