



Universal Remote Control Dimmers 300W Comfort

Technical Characteristics

Fixing mode	Din-Rail
Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Supply voltage	230V +10% / -15%
Fuse	with electronic short-circuit and overload protection
Depth of installed product	65 mm
Height of installed product	90 mm
Width of installed product	17.5 mm
Halogen switching capacity 230V	300 W
Power consumed	2.1 W
Power consumption (operation)	2.1 W
Incandescent bulb power	300 W
Total power loss under IN	0.2 W
Number of modules	1
RAL colour	RAL 9001 - Cream
Surface appearance	matt
Max. power with incandescent lamps	300 W
Mounting type	din-Rail
Connection cross-sect. flexible conductor	1,5 / 6mm ²
Connection cross-sect. rigid cable	1,5 / 6mm ²
Type of load	universal
Type of connection	with screw
Type of connection	with screw terminals
Dimming principle	automatic load detection
Protection index IP	IP20
Operating temperature	45 °C -10 °C