

# EVN004

## Remote Control Dimmer universal 500W



- Architecture
  - Fixing mode  
Din-Rail
- Main electrical features
  - Frequency  
50/60 Hz
- Voltage
  - Supply voltage  
230V +10% / -15%
- Fuse
  - Fuse  
with electronic short-circuit and overload protection
- Dimensions
  - Depth of installed product  
62 mm
  - Height of installed product  
85 mm
  - Width of installed product  
35 mm
- Power
  - Power consumed  
4.5 W
  - Power consumption (operation)  
4.5 W
  - Total power loss under IN  
0.2 W
- Capacity

- Number of modules  
2
- Materials
  - RAL colour  
RAL 9001 - Cream
  - Surface appearance  
matt
- Incandescent bulbs control
  - Max. power with incandescent lamps  
500 W
- Installation, mounting
  - Mounting type  
din-Rail
- Connection
  - Connection cross-sect. flexible conductor  
1 / 6mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1 / 6mm<sup>2</sup>
  - Type of load  
universal
  - Type of connection  
with screw
  - Type of connection  
with screw terminals
- Settings
  - Setting  
Reset of settings for special functions, setting of comfort functions (1...4) via adjusting wheel
- Equipment
  - Dimming principle  
automatic load detection
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-20/50 °C
- Temperature
  - Operating temperature  
-20/50 °C