

EVN002

Remote Control Dimmer universal 500W



- Architecture
 - Fixing mode
Din-Rail
- Main electrical features
 - Frequency
50/60 Hz
- Voltage
 - Supply voltage
230V +10% / -15%
- Fuse
 - Fuse
with electronic short-circuit and overload protection
- Dimensions
 - Depth of installed product
62 mm
 - Height of installed product
85 mm
 - Width of installed product
35 mm
- Power
 - Power consumed
4.5 W
 - Power consumption (operation)
4.5 W
 - Total power loss under IN
0.2 W
- Capacity

- Number of modules
2
- Materials
 - RAL colour
RAL 9001 - Cream
 - Surface appearance
matt
- Incandescent bulbs control
 - Max. power with incandescent lamps
500 W
- Installation, mounting
 - Mounting type
din-Rail
- Connection
 - Connection cross-sect. flexible conductor
1,5 / 6mm²
 - Connection cross-sect. rigid cable
1,5 / 6mm²
 - Type of load
universal
 - Type of connection
with screw
 - Type of connection
with screw terminals
- Equipment
 - Dimming principle
automatic load detection
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-20/50 °C
- Temperature
 - Operating temperature
-20/50 °C