

TXM616D

Output module 16x 16A (C)/230V~, KNX



Architecture

Number of outputs	16
Bus system	yes
Fixing mode	REG

Functions

Function	with positioning function for blind and lamella position ; with safety functions e.g. for wind, rain, alarm ; with sun shade function
----------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Connectivity

Bus system radio frequent	No
---------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
Rated current	16 A

Dimensions

Height 90 mm

Frequency

Frequency 50;60 Hz

Power

Max. power with electronic transfo. 1500 W

Capacity

Breaking capacity 16A 250V AC1

Capacity

Number of modules 8

Materials

Colour light grey

LED control

Lighting power LED lamps 450 W

Incandescent bulbs control

Max. power with incandescent lamps 2300 W

Connection

Connection cross-sect. flexible conductor 0,5 ; 4mm²

Connection cross-sect. rigid cable 0,5 ; 6mm²

Type of load C-Load

Type of connection with screw

Type of contacts 16F

Type of connection with screw terminals

Settings

Setting Switching time on change of direction is preset

Safety

Protection index IP IP20

Use conditions

Operating temperature -5/45 °C

Storage temperature -20/70 °C

Temperature

Operating temperature -5/45 °C
