

# EVN011

## Remote Control Dimmer universal 300W



### Architecture

Fixing mode Din-Rail

### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50;60 Hz

### Voltage

Supply voltage 230V +10% ; -15%

### Fuse

Fuse with electronic short-circuit and overload protection

### Dimensions

Depth of installed product 65 mm

Height of installed product 90 mm

Width of installed product 17.5 mm

### Power

Halogen switching capacity 230V	300 W
Power consumed	2.1 W
Power consumption (operation)	2.1 W
Incandescent bulb power	300 W
Total power loss under IN	0.2 W

#### Capacity

Number of modules	1
-------------------	---

#### Materials

RAL colour	RAL 9001 - Cream
Surface appearance	matt

#### LED control

Lighting power LED lamps	60 W
--------------------------	------

#### Incandescent bulbs control

Max. power with incandescent lamps	300 W
------------------------------------	-------

#### Installation, mounting

Mounting type	din-Rail
---------------	----------

#### Connection

Connection cross-sect. flexible conductor	1,5 ; 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 ; 6mm <sup>2</sup>
Type of load	universal
Type of connection	with screw
Type of connection	with screw terminals

#### Equipment

Dimming principle	automatic load detection
-------------------	--------------------------

#### Safety

Protection index IP	IP20
---------------------	------

#### Use conditions

Operating temperature	-10/45 °C
Storage temperature	-25/70 °C

#### Temperature

Operating temperature	-10/45 °C
-----------------------	-----------