



### MCB 3P 6kA C-32A 3M

#### Technical Characteristics

Number of poles	3 P
Type of pole	3 P
Curve	C
Rated operational voltage U <sub>e</sub>	230 V 400 V
Frequency	50/60 Hz
Rated current	32 A
Type of supply voltage	AC
Rated insulation voltage	500 V
Rated impulse withstand voltage	4000 V
Rated service breaking capacity I <sub>cs</sub> AC according IEC 60898-1	6 kA
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	52.5 mm
Electric endurance in number of cycles	4000
Number of mechanical operations	20000
Number of modules	3
Tightening torque	2,8Nm
Connection cross-sect. flexible conductor	1 / 25mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 35mm <sup>2</sup>
Type of connection	with screw
Standard text	EN 60898-1
Protection index IP	IP20
Operating temperature	-25 °C 70 °C