

WMSSU83/3A

Switched Fused Spur Fitted with 3A Fuse



- Configuration
 - Switch mode
2pole
- Fuse
 - Fuse
with ceramic fine fuse F 3A
- Dimensions
 - Depth
30.3 mm
 - Height
86 mm
 - Width
86 mm
- Frequency
 - Frequency
50/60 Hz
- Materials
 - Material
Urea-formaldehyde
- Installation, mounting
 - Imprint
with clear terminal markings
- Cable
 - Wiring
with double earth connection
- Scope of delivery
 - Component

with 2 fixing screws M3.5 x 30 mm

- Equipment
 - Lighting
 - without lighting (cannot be illuminated)
- Standards
 - Standard
 - BS 1363-4
- Safety
 - Protection
 - to protect downstream loads