



KNX glass sensor 2g thermostat, display, intg bus coupl. , KNX-TS sensor, bl.

Technical Characteristics

| | |
|---|--|
| Fixing mode | flush-mounting |
| Function | for switch, push-button, dimmer, blind and thermostat functions with valve protection function |
| Operating voltage | 21 ... 32 V DC |
| Depth | 37.7 mm |
| Height | 160 mm |
| Width | 86 mm |
| Current consumption | 23 mA |
| Colour | black |
| RAL colour | RAL 9005 - Jet black |
| Material | glass |
| Surface appearance | glossy |
| Type of surface treatment | Tampography |
| Inscribable, with labelling field | No |
| Protection index IP | IP20 |
| Operating temperature | 45 °C -5 °C |
| Designation syntax: Core designation/function | Glass sensor |
| Application, usage | KNX - operating systems |