



Auxiliary contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)

Technical Characteristics

Fixing mode	Clipped
Rated operational voltage Ue	230 V
Total power loss under IN	3 W
Type of connection	quick connect
Type of contacts	1 NO/NC
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP4X