

Product data sheet

HXA024H

:hager



Alarm contact 1NO+1NC 250V AC (x160-P160-x250-P250-x630-P630)

Technical Characteristics

Fixing mode	Clipped
Rated operational voltage Ue	250 V
Rated current	3 A
Type of supply voltage	AC/DC
Rated impulse withstand voltage	1500 V
Total power loss under IN	3 W
Type of connection	quick connect
Type of contacts	1 NO/NC
Number of auxiliary contacts as change-over contact	1
European directive RoHs	voluntary compliance
European directive WEEE	concerned
Protection index IP	IP4X