



13A FCU Switched with LED Indicator and Flex Outlet Marked EXTRACT FAN

Technical Characteristics

Switch mode	2pole
Frequency	50/60 Hz
Rated current	13 A
Fuse	with ceramic fine fuse F 13A
Depth	30.3 mm
Height	86 mm
Width	86 mm
Colour	white
Material	Urea-formaldehyde
Imprint	with clear terminal markings
Wiring	with double earth connection
Component	with 2 fixing screws M3.5 x 30 mm
Lighting	with control LED for ON
Standard	BS 1363-4
Protection	to protect downstream loads