

Product data sheet

ECM300C

hager



3 Phase kWhmeter via CT 1A or 5A 4M MBUS MID

Technical Characteristics

Bus system	M-BUS
Type of pole	3P+N
Fixing mode	DIN rail type O (symmetrical)
Pulsed output	
Frequency	50 Hz
Type of supply voltage	AC
Type of measuring instrument	electronical
Supply voltage	400 V \pm 20%
Colour	
RAL colour number	
Tightening torque	0.5Nm
Mounting type	din-Rail
Connection cross-sect. flexible conductor	
Connection cross-sect. rigid cable	
Connection type	
Type of display	retro illuminated display
Type of programmable thermostat	
Type of counter	4 wires counter
European directive WEEE	concerned
Protection index IP	IP20
Protection class	isol.class II