



Fuse carrier 1P 1000V DC L38 1M

Technical Characteristics

Number of poles	1 P
Type of pole	1 P
Indicator lamp	no
Rated operational voltage Ue	690 V 1000 V
Frequency	50 Hz
Rated current	32 A
Type of supply voltage	DC
Rated insulation voltage	690 V
Depth of installed product	75 mm
Height of installed product	77 mm
Width of installed product	18 mm
Total power loss under IN	1.1 W
Electric endurance in number of cycles	2000
Number of mechanical operations	5000
Number of modules	1
Interlockable	No
Tightening torque	2Nm
Connection cross-sect. flexible conductor	10mm ²
Connection cross-sect. rigid cable	16mm ²
Can be accessorized	No
European directive WEEE	concerned
Protection index IP	IP20