



168578

IP21

Crystal Ball, TS Crystal Ball, glass clear, mirrored

Technical Characteristics

Switch mode	Normally open contact
Operating voltage	8 ... 30 V DC
Depth	5 mm
Height	160 mm
Width	86 mm
Dimensions (W x H x D)	86 x 160 x 5 mm
Material	glass
Surface appearance	mirrored
Type of connection	with screw terminals
Designation syntax: Core designation/function	Crystal Ball