

# 41092045

SCHUKO soc.out. LEDorient.,enhncd contact prot.,screw-in lift term.,R.cl,bl.

:hager

- Main electrical features
  - Nominal voltage  
250 V
  - Rated voltage  
250 V AC
  - Rated current  
16 A
- Frequency
  - Frequency  
50/60 Hz
- Capacity
  - Number of modules  
1
- Cover, door
  - Cover  
Central cover plate
- Materials
  - Colour  
black
  - Colour  
deep black
  
  - RAL colour  
RAL 9005 - Jet black
  - Material  
thermoplastic

- Surface appearance  
glossy
- Installation, mounting
  - Imprint  
without imprint
- Connection
  - Connection terminals  
according to IEC 60884-1
  - Type of connection  
with screw-in lift terminals
- Cable
  - Wiring  
through-wiring possible, therefore also ideal for retrofitting
- Equipment
  - Lighting  
additional benefit by combination of a socket outlet with an orientation light
- Safety
  - Protection index IP  
IP20
  - Protection  
Enhanced contact protection
- Identification
  - Designation syntax: Core designation/function  
SCHUKO socket outlet