

SM601

Digital ammeter 0-600A indirect reading



- Architecture
 - Fixing mode
Din-Rail
- Main electrical features
 - Frequency
45/65 Hz
- Dimensions
 - Depth of installed product
54 mm
 - Height of installed product
85 mm
 - Width of installed product
70 mm
- Power
 - Power consumed
1 VA
 - Total power loss under IN
1.1 W
- Measurement
 - Type of measuring instrument
ammeter
- Capacity
 - Number of modules
4
- Installation, mounting
 - Mounting type
din-Rail

- Connection
 - Connection cross-sect. flexible conductor
6mm²
 - Connection cross-sect. rigid cable
10mm²
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-40/70 °C
- Temperature
 - Operating temperature
-10/55 °C