

WNE040BG

cubyko 2-gang 2-way switch flush mounted white IP55 with claws

:hager

- Architecture
 - Fixing mode
Screwed
- Controls and indicators
 - Indicator lamp
as an accessory
- Main electrical features
 - Frequency
50/60 Hz
 - Rated current
10 AX
- Dimensions
 - Depth of installed product
40 mm
 - Height of installed product
75 mm
 - Dimensions (LLxwwxhh)
83X83X36
 - Width of installed product
75 mm
- Materials
 - RAL colour
RAL 9010 - Pure white
 - RAL colour number
9010
 - Material
Polypropylen

- Connection
 - Connection cross-sect. rigid cable
mini 2x1 mm² - maxi 2x2,5 mm²
 - Type of connection
Quickconnect
 - Type of contacts
2 way
- Accessories included
 - Inscrivable, with labelling field
No
- Safety
 - Protection index IP
IP20
- Use conditions
 - Storage temperature
-50/50 °C
- Temperature
 - Operating temperature
-40/30 °C