

EPN518

Latching relay 1NC+1NO 24V

Main electrical features

Rated operational voltage Ue	250 V
Frequency	50;60 Hz
Rated current	16 A

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	1.2 W
---------------------------	-------

Endurance

Number of mechanical operations	500000
---------------------------------	--------

Capacity

Number of modules 1

Installation, mounting

Tightening torque 1,6Nm

Connection

Connection cross-sect. flexible conductor 1 ; 6mm²

Connection cross-sect. rigid cable 1,5 ; 10mm²

Type of connection with screw

Number of contacts 2

Type of contacts 1NC+1NO

Equipment

Can be accessorized No

Standards

European directive WEEE concerned

Safety

Protection index IP IP20

Use conditions

Storage temperature -40/80 °C

Temperature

Operating temperature -5/40 °C
