

EPN519

Latching relay 1NC+1NO 12V



Main electrical features

Rated operational voltage Ue	250 V
Frequency	50;60 Hz
Rated current	16 A

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Power

Total power loss under IN	1.2 W
---------------------------	-------

Endurance

Number of mechanical operations	500000
---------------------------------	--------

Capacity

Number of modules	1
-------------------	---

Connection

Connection cross-sect. flexible conductor 1 ; 6mm²

Connection cross-sect. rigid cable	1,5 ; 10mm ²
------------------------------------	-------------------------

Type of connection	with screw
--------------------	------------

Number of contacts	2
--------------------	---

Type of contacts	1NC+1NO
------------------	---------

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Storage temperature	-40/80 °C
---------------------	-----------

Temperature

Operating temperature	-5/40 °C
-----------------------	----------
