

# EPN520

Latching relay 2NO 230V



- Main electrical features
  - Rated operational voltage  $U_e$   
250 V
  - Frequency  
50;60 Hz
  - Rated current  
16 A
- Voltage
  - Rated insulation voltage  
250 V
- Dimensions
  - Depth of installed product  
63 mm
  - Height of installed product  
83 mm
  - Width of installed product  
17.5 mm
- Power
  - Total power loss under IN  
2.4 W
- Endurance
  - Number of mechanical operations  
500000
- Capacity
  - Number of modules  
1
- Installation, mounting

- Tightening torque  
1,6Nm
- Connection
  - Connection cross-sect. flexible conductor  
1 ; 6mm<sup>2</sup>
  - Connection cross-sect. rigid cable  
1,5 ; 10mm<sup>2</sup>
  - Type of connection  
with screw
  - Number of contacts  
2
  - Type of contacts  
2NO
- Equipment
  - Can be accessorized  
No
- Standards
  - European directive WEEE  
concerned
- Safety
  - Protection index IP  
IP20
- Use conditions
  - Storage temperature  
-40/80 °C
- Temperature
  - Operating temperature  
-5/40 °C