

# EPN528

Latching relay 2NC+2NO 24V



## Main electrical features

Rated operational voltage Ue	250 / 400 V
Frequency	50;60 Hz
Rated current	16 A

## Voltage

Rated insulation voltage	400 V
--------------------------	-------

## Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	35 mm

## Power

Total power loss under IN	2.4 W
---------------------------	-------

## Endurance

Number of mechanical operations	500000
---------------------------------	--------

---

Capacity

Number of modules	2
-------------------	---

---

Connection

Connection cross-sect. flexible conductor 1 ; 6mm<sup>2</sup>

Connection cross-sect. rigid cable	1,5 ; 10mm <sup>2</sup>
------------------------------------	-------------------------

---

Type of connection	with screw
--------------------	------------

---

Number of contacts	2
--------------------	---

---

Type of contacts	2NC+2NO
------------------	---------

---

Standards

European directive WEEE	concerned
-------------------------	-----------

---

Safety

Protection index IP	IP20
---------------------	------

---

Use conditions

Storage temperature	-40/80 °C
---------------------	-----------

---

Temperature

Operating temperature	-5/40 °C
-----------------------	----------

---