

# EPN540

## Latching relay 4NO 230V

### Main electrical features

Rated operational voltage Ue	250 / 400 V
Frequency	50;60 Hz
Rated current	16 A

### Voltage

Rated insulation voltage	400 V
--------------------------	-------

### Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	35 mm

### Power

Total power loss under IN	4.8 W
---------------------------	-------

### Endurance

Number of mechanical operations	500000
---------------------------------	--------

---

Capacity

Number of modules 2

---

Installation, mounting

Tightening torque 1,6Nm

---

Connection

Connection cross-sect. flexible conductor 1 ; 6mm<sup>2</sup>

---

Connection cross-sect. rigid cable 1,5 ; 10mm<sup>2</sup>

---

Type of connection with screw

---

Number of contacts 4

---

Type of contacts 4NO

---

Equipment

Can be accessorized No

---

Standards

European directive WEEE concerned

---

Safety

Protection index IP IP20

---

Use conditions

Storage temperature -40/80 °C

---

Temperature

Operating temperature -5/40 °C

---