

Product data sheet

NDN432A

:hager



MCB 4P 10kA/15kA D-32A 4M

Technical Characteristics

Neutral position	without neutral
Number of poles	4 P
Type of pole	4 P
Fixing mode	Din-Rail
Curve	D
Rated operational voltage U _e	400 V
Rated current	32 A
Type of supply voltage	AC
Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V
Rated service breaking capacity I _{cs} AC according IEC 60898-1	7.5 kA
Rated service breaking capacity I _{cs} under 400V AC according IEC 60947-2	7.5 kA
Rating current 30°C	32 A
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	70 mm
Total power loss under I _N	16.5 W
Electric endurance in number of cycles	4000
Number of mechanical operations	20000
Number of modules	4
Tightening torque	2,8Nm
Can be accessorized	Yes
Standard text	EN 60898-1 IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP20