

# CR64AX/1.0LSF/4

CR64AX c/w 4 Core 1mm<sup>2</sup> 4m LSOH Lead

## Main electrical features

Rated operational voltage U <sub>e</sub>	207 / 230 / 253 V
Rated current	6 A

## Materials

Colour	pure white
--------	------------

## Connection

Cable End	Prepared - end of barrel closed
-----------	---------------------------------

## Cable

Conductor Size	1 mm <sup>2</sup>
Cable Material	Low Smoke Zero Halogen
Cable length	4000 mm
Cable Standard	BS 6500

## Equipment

Number of terminations -sockets	5
Number of terminations -plugs	4

Technical characteristics CR64AX/1-0LSF4-A

Contact Material	Phosphor Bronze
Use	
Mechanical Load	5 Kg maximum
Safety	
Inflammability	UL 94 V0
Identification	
Application, usage	Light control