



# Product data sheet

NCN306A

**:hager**



## MCB 3P 10kA/15kA C-6A 3M

### Technical Characteristics

Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P
Fixing mode	Din-Rail
Curve	C
Rated operational voltage Ue	400 V
Rated current	6 A
Type of supply voltage	AC
Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V
Rated service breaking capacity Ics AC according IEC 60898-1	7.5 kA
Rated service breaking capacity Ics under 400V AC according IEC 60947-2	7.5 kA
Rating current 30°C	6 A
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	52.5 mm
Total power loss under IN	4.06 W
Electric endurance in number of cycles	4000
Number of mechanical operations	20000
Number of modules	3
Tightening torque	2,8Nm
Can be accessorized	Yes
Standard text	EN 60898-1 IEC 60947-2
European directive WEEE	concerned
Protection index IP	IP20