

SPN240D

SPD 2P pluggable 40kA class 2 with end of life indicator



Architecture

Neutral position	left
Number of poles	2 P
Type of pole	1P+N

Controls and indicators

Indicator lamp	end of life indicator
----------------	-----------------------

Connectivity

With remote signalling contact	No
--------------------------------	----

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50;60 Hz

Electric current

Max discharge (I _{max}) or impulse (I _{imp})	40 kA
--	-------

Dimensions

Width of installed product	36 mm
<hr/>	
Power	
Total power loss under IN	0 W
<hr/>	
Capacity	
Number of modules	2
<hr/>	
Installation, mounting	
Tightening torque	3,6Nm
Mounting type	din-Rail
<hr/>	
Connection	
Connection cross-sect. flexible conductor	25mm ²
Connection cross-sect. rigid cable	35mm ²
<hr/>	
Standards	
European directive WEEE	concerned
<hr/>	
Safety	
Protection index IP	IP20
<hr/>	
Use conditions	
Storage temperature	-40/80 °C
<hr/>	
Temperature	
Operating temperature	-40/55 °C
<hr/>	