

KRN190

Neutral connecting block 100A

Architecture

Number of poles	1 P
Type of pole	N
Fixing mode	DIN rail type O (symmetrical)

Main electrical features

Rated operational voltage Ue	230 / 400 V
Rated current	100 A
Type of supply voltage	AC

Voltage

Rated insulation voltage	440 V
--------------------------	-------

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

Capacity

Technical characteristics KRN190

Number of modules	1
Installation, mounting	
Tightening torque	3,6Nm
Standards	
European directive WEEE	concerned
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-20/50 °C