

ESC002

Sealing cover for 2M contactor



Main electrical features

Rated operational voltage Ue	250 V
Rated current	5 A

Voltage

Rated insulation voltage	250 V
--------------------------	-------

Electric current

Acceptable current rating with AC1	5 A
------------------------------------	-----

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	9 mm

Power

Total power loss under IN	0.4 W
---------------------------	-------

Capacity

Number of modules	0.5
-------------------	-----

Connection

Connection cross-sect. flexible conductor 1 ; 6mm ²	
----------------------------------------------------------------	--

Connection cross-sect. rigid cable	1,5 ; 10mm ²
------------------------------------	-------------------------

Type of connection	with screw
--------------------	------------

Number of contacts	2
--------------------	---

Type of contacts	1NC+1NO
------------------	---------

Standards

European directive WEEE	not concerned
-------------------------	---------------

Use conditions

Storage temperature	-25/80 °C
---------------------	-----------

Temperature

Operating temperature	-10/50 °C
-----------------------	-----------
