

# ESC003

## Sealing cover for 3M contactor



### Main electrical features

Rated operational voltage $U_e$	250 V
---------------------------------	-------

Rated current	5 A
---------------	-----

### Voltage

Rated insulation voltage	250 V
--------------------------	-------

### Electric current

Acceptable current rating with AC1	5 A
------------------------------------	-----

### Dimensions

Depth of installed product	60 mm
----------------------------	-------

Height of installed product	83 mm
-----------------------------	-------

Width of installed product	9 mm
----------------------------	------

### Power

Total power loss under IN	0.4 W
---------------------------	-------

### Capacity

Number of modules	3
-------------------	---

---

Connection

Connection cross-sect. flexible conductor 1 ; 6mm <sup>2</sup>	
----------------------------------------------------------------	--

---

Connection cross-sect. rigid cable	1,5 ; 10mm <sup>2</sup>
------------------------------------	-------------------------

---

Type of connection	with screw
--------------------	------------

---

Number of contacts	2
--------------------	---

---

Type of contacts	1NC+1NO
------------------	---------

---

Standards

European directive WEEE	not concerned
-------------------------	---------------

---

Use conditions

Storage temperature	-25/80 °C
---------------------	-----------

---

Temperature

Operating temperature	-10/50 °C
-----------------------	-----------

---