

ESC080

Auxiliary contact 6A, 1NO+1NC



Main electrical features

Rated operational voltage U_e	230 V
Rated current	6 A

Voltage

Rated insulation voltage	240 V
Rated impulse withstand voltage	4 kV

Electric current

Acceptable current rating with AC1	6 A
------------------------------------	-----

Dimensions

Depth of installed product	60 mm
Height of installed product	83 mm
Width of installed product	11 mm

Power

Total power loss under I_N	0.1 W
------------------------------	-------

Endurance

Electric endurance in number of cycles	30000
Number of mechanical operations	1000000

Capacity

Number of modules	0.5
-------------------	-----

Connection

Connection cross-sect. flexible conductor	1 ; 6mm ²
Connection cross-sect. rigid cable	1 ; 6mm ²
Type of connection	with screw
Number of contacts	2
Type of contacts	1NC+1NO

Standards

European directive WEEE	concerned
-------------------------	-----------

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Storage temperature	-40/80 °C
---------------------	-----------

Temperature

Operating temperature	-10/50 °C
-----------------------	-----------