

FL110A

Steel enclosure, Orion.Plus, plain door 500x300x200 mm

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	200 mm
----------------------------	--------

Height of installed product	500 mm
-----------------------------	--------

Width of installed product	300 mm
----------------------------	--------

Capacity

Number of modules	30
-------------------	----

Cover, door

Type of door closing	lock with male triangular wrench
----------------------	----------------------------------

Number of keylock of the door 1	
---------------------------------	--

Interlockable	Yes
---------------	-----

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
RAL colour number	7035
Material	Steel
Type of surface treatment	powder-coated

Equipment

Number of rows	3
Quantity of section in width	0
Can be accessorized	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP65
Protection class	isol.class I