

FL124A

Steel enclosure, Orion.Plus, plain door 800x600x300 mm



Architecture

Fixing mode	surface-mounting
-------------	------------------

Dimensions

Depth of installed product	300 mm
----------------------------	--------

Height of installed product	800 mm
-----------------------------	--------

Width of installed product	600 mm
----------------------------	--------

Capacity

Number of modules	130
-------------------	-----

Cover, door

Type of door closing	lock with male triangular wrench
----------------------	----------------------------------

Number of keylock of the door 2	
---------------------------------	--

Interlockable	Yes
---------------	-----

Materials

Colour	RAL 7035
--------	----------

Colour	light grey
--------	------------

Technical characteristics FL124A

RAL colour	RAL 7035 - Light grey
RAL colour number	7035
Material	Steel
Type of surface treatment	powder-coated
Equipment	
Number of rows	5
Safety	
Protection index IP	IP65
Protection class	isol.class I