

FL126A

Steel enclosure, Orion.Plus, plain door 950x600x300 mm

Architecture

Fixing mode	surface-mounting
-------------	------------------

Main electrical features

Rated current	630 A
---------------	-------

Dimensions

Depth of installed product	300 mm
----------------------------	--------

Height of installed product	950 mm
-----------------------------	--------

Width of installed product	600 mm
----------------------------	--------

Capacity

Number of modules	156
-------------------	-----

Cover, door

Type of door closing	lock with male triangular wrench
----------------------	----------------------------------

Number of keylock of the door	2
-------------------------------	---

Interlockable	Yes
---------------	-----

Materials

Colour	RAL 7035
Colour	light grey
RAL colour	RAL 7035 - Light grey
RAL colour number	7035
Material	Steel
Type of surface treatment	powder-coated

Equipment

Number of rows	6
Quantity of section in width	0
Can be accessorized	No

Standards

European directive WEEE	not concerned
-------------------------	---------------

Safety

Protection index IP	IP65
Protection class	isol.class I